

ETP™ 5000S Steel EMT Set Screw Couplings

NEC/CEC:
Listed for Ordinary Locations

Application

- To ground and secure EMT raceway sections together.

Features

- Heavy steel walls.
- Concretetight when taped.
- Pre-set/pre-staked set screws.
- Three-way combination screws 1/2" thru 2".
- Slotted hexhead screw 2-1/2" thru 4".
- 2-1/2" thru 4" rated for threadless aluminum or steel RMC and IMC conduit.

Material/Finish

- Steel/zinc plated

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: (1/2 - 2) E-14895, E-11853
- UL Listed: (2-1/2 - 4) E-11853
- CSA Standard: C22.2 No. 18.3
- cUL Listed: E-14895
- CSA Certified: 028507
- NEMA: FB-1



5050S — 5100S



5125S — 5400S

Trade Size (Inches)	Dimensions in Millimeters (Inches)			Weight per 100 kg (lb)	Catalog Number
	Body Length	Maximum Diameter			
1/2	44.5 (1.75)	21.3 (0.84)		4.54 (10.00)	5050S
3/4	54.1 (2.13)	27.4 (1.08)		7.26 (16.00)	5075S
1	63.5 (2.50)	33.3 (1.31)		1.34 (25.00)	5100S
1-1/4	82.6 (3.25)	42.9 (1.69)		0.41 (45.00)	5125S
1-1/2	95.3 (3.75)	49.3 (1.94)		7.22 (60.00)	5150S
2	101.6 (4.00)	60.5 (2.38)		7.19 (82.00)	5200S
2 - 1/2	101.6 (4.00)	47.4 (2.93)		5.30 (166.0)	5250S
3	108.0 (4.25)	90.4 (3.56)		6.62 (213.0)	5300S
3 - 1/2	114.3 (4.50)	103.1 (4.06)		7.93 (260.0)	5350S
4	120.7 (4.75)	116.8 (4.60)		6.08 (300.0)	5400S