


Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States




Our Quick Ship Program is a world-class fulfillment program that allows for fast shipment of select Appleton LED products to maximize speed and responsiveness. It leverages our local infrastructure, local presence, and our commitment to service to help you avoid downtime, stay on schedule, respond to the unexpected, and control costs in today's challenging environments.

Put Emerson's wealth of resources and expertise to work for you with our made-to-stock products – shipped within 5 days of order receipt to continental US locations^⓪. Contact us about your specific requirements at 800-621-1506 or locate a representative in your area at www.masteringled.com.


Areamaster™ Generation 2 Series | Low Lumen

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	9000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLGL6CG6BU	5
	15000	5000K	Clear Glass	NEMA 7x7		AMLGL7CG6BU	10
	15000	5000K	Clear Glass	NEMA 7x6	347-480 Vac, 50/60 Hz	AMLGL7CG7BH	10
	15000	5000K	Clear Glass	NEMA 7x7		AMLGL7CG6BH	5
	19000	5000K	Clear Glass	NEMA 7x6	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLGL8CG7BU	5
	19000	5000K	Clear Glass	NEMA 7x7		AMLGL8CG6BU	5
	19000	5000K	Clear Glass	NEMA 7x7	347-480 Vac, 50/60 Hz	AMLGL8CG6BH	10





Areamaster Generation 2 Series | High Lumen

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	24000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLHL1CG6BU	5
	24000	5000K	Clear Glass	NEMA 7x7		AMLHL1CG6BH	10

Industrial Areamaster Generation 2 Series | Low Lumen

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	15000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	IAMLGL7CG6BU	5
	19000	5000K	Clear Glass	NEMA 7x6		IAMLGL8CG7BU	10

Areamaster Accessories

	Description	Catalog Number	Max. Qty.
	Pipe or Wall Mount Bracket Used with GAM8CA Clamps to 1" to 2-1/2" pipe	GAM8WB	5
	Poletop Slip-Fitter Slip-fits 1-1/2" or 2" pipe size poletop tenons	GSF20	10
	Poletop Slip-Fitter Slip-fits 2" or 2-1/2" pipe size poletop tenons	GAM8SF	10
	Safety Cable Stainless steel	LEDSC	10

Industrial Baymaster™ LED Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	19500	5000K	Clear Glass Lens	Medium	120-277 Vac, 50/60 Hz; 125-300 Vdc	IBLLPL8CGMNBU	5


^⓪ Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.




Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States




Mercmaster™ Connect LED Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	9500	5000K	Clear Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	MGCL9CP5BU7P	5


Mercmaster™ LED Generation 3 Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
		5000K	Diffused Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	MLGL9CD5BU	10

Mercmaster LED Low Profile Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	100-277 Vac, 50/60 Hz; 125-300 Vdc	MLLED4CD5BU	15
	7500	5000K	Diffused Polycarbonate Globe	Type V		MLLED7CD5BU	10

Industrial Mercmaster LED Low Profile Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	100-277 Vac, 50/60 Hz; 125-300 Vdc	IMLLED4CD5BU	10
	7500	5000K	Diffused Polycarbonate Globe	Type V		IMLLED7CD5BU	10



Contender™ LED Series †

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	VMV5LCD5BU	10

Mercmaster Accessories

	Description	Catalog Number	Max. Qty.
	Mounting Hood Pendant One Hub, Rigid Mounting 3/4" NPT	KPA75	20
	Mounting Hood Ceiling Five Hubs, Four Close-Up Plugs 3/4" NPT	KPC75	20
	Mounting Hood Wall Five Hubs, Four Close-Up Plugs 3/4" NPT	KPWB75	20
	Mounting Hood 25° Stanchion One Hub 1-1/2" NPT	KPS150	20
	Mounting Hood 25° Stanchion One Hub 1-1/4" NPT	KPS125	10
	Mounting Hood 90° Stanchion One Hub 1-1/2" NPT	KPST150	10
	Mounting Hood Adapter Crouse-Hinds™ Champ® † Pendant, Flexible Pendant, Ceiling	MMADCHVS	10
	Mounting Hood Adapter Crouse-Hinds™ Champ® † Wall, 25° and 90° Angle Stanchion	MMADCHVA	10
	Visor Dark Sky Compliant	MMVISOR	10

Mercmaster and Contender Accessories

	Description	Catalog Number	Max. Qty.
	Globe Guard Stainless steel wire	MGU1	15
	Safety Cable Stainless steel	LEDSC	10


Ⓢ Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.

† Mounts directly to the following Crouse Hinds™ Champ® VMV mounting hoods. | Crouse-Hinds is a registered trademark of Cooper Industries, Inc.





Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States





Code • Master Accessories			
	Description	Catalog Number	Max. Qty.
	Lens Guard Stainless Steel Wire	CMLEDGU	5


Rigmaster™ LED Series							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	8000	5000K	Clear Polycarbonate Lens	4 ft Linear	120-277 Vac, 50/60 Hz; 125-300 Vdc	RMA42CPLBUNGW2	15


Rigmaster Accessories			
	Description	Catalog Number	Max. Qty.
	Safety Cable Stainless steel	LEDSC	10

Retromaster LED Series						
	Lumens	CCT	Globe Material/Diffusion	Voltage	Catalog Number	Max. Qty.
	1000 or 2000 (Selectable)	5000K	Diffused Polycarbonate Lens	120-277 Vac, 50/60 Hz	RETROLEDV1BU	5
	3500 or 5000 (Selectable)	5000K	Diffused Polycarbonate Lens	120-277 Vac, 50/60 Hz	RETROLEDV5BU	5

HEX LED Series				
	Description	Voltage	Catalog Number	Max. Qty.
	Exit and Emergency Combo Double-sided, Red Lettering 120 Vac Surge Voltage, 12 Vdc Battery	120-277 Vac, 60 Hz	HEXC122R1212	5

IHC LED Series							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	60000	5000K	Clear Polycarbonate Lens	Medium	277-480 Vac, 50/60 Hz	IHCN62CPMBHGP	5

IHC Accessories			
	Description	Catalog Number	Max. Qty.
	Mounting Bracket Ceiling, Wall, Column, Floor and Conduit Mounting Options Retrofits with a variety of existing mounting hardware	IHCBRKTL	5

IWL LED Series							
	Lumens	CCT	Lens Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	6000, 8000, or 10000 Selectable	3000K, 4000K, or 5000K Selectable	Diffused Glass Lens	Type III	120-277 Vac, 50/60 Hz	IWL10LZG3BU	5

① Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.

