



# Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States








Our Quick Ship Program is a world-class fulfillment program that allows for fast shipment of select Appleton LED products to maximize speed and responsiveness. It leverages our local infrastructure, local presence, and our commitment to service to help you avoid downtime, stay on schedule, respond to the unexpected, and control costs in today's challenging environments.


Put Emerson's wealth of resources and expertise to work for you with our made to stock products – shipped within 5 days of order receipt to continental US locations <sup>Ⓛ</sup>. Contact us about your specific requirements at 800-621-1506 or locate a representative in your area at [www.masteringled.com](http://www.masteringled.com).

Areamaster™ Generation 2 Series   Low Lumen							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	9000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLGL6CG6BU	5
	15000	5000K	Clear Glass	NEMA 7x7		AMLGL7CG6BU	10
	15000	5000K	Clear Glass	NEMA 7x6	347-480 Vac, 50/60 Hz	AMLGL7CG7BH	10
	15000	5000K	Clear Glass	NEMA 7x7		AMLGL7CG6BH	5
	19000	5000K	Clear Glass	NEMA 7x6	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLGL8CG7BU	5
	19000	5000K	Clear Glass	NEMA 7x7		AMLGL8CG6BU	5
	19000	5000K	Clear Glass	NEMA 7x7	347-480 Vac, 50/60 Hz	AMLGL8CG6BH	10

Areamaster Generation 2 Series   High Lumen							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	24000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLHL1CG6BU	5
	24000	5000K	Clear Glass	NEMA 7x7		347-480 Vac, 50/60 Hz	AMLHL1CG6BH

Industrial Areamaster Generation 2 Series   Low Lumen							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	15000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	IAMLGL7CG6BU	5
	19000	5000K	Clear Glass	NEMA 7x6		120-277 Vac, 50/60 Hz, 125-300 Vdc	IAMLGL8CG7BU

Areamaster Accessories							
	Description					Catalog Number	Max. Qty.
	Pipe or Wall Mount Bracket   Used with GAM8CA   Clamps to 1" to 2-1/2" pipe					GAM8WB	5
	Poletop Slip-Fitter   Slip-fits 1-1/2" or 2" pipe size poletop tenons					GSF20	10
	Poletop Slip-Fitter   Slip-fits 2" or 2-1/2" pipe size poletop tenons					GAM8SF	10
	Safety Cable   Stainless steel					LEDSC	10

Industrial Baymaster™ LED Series							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	19500	5000K	Clear Glass Lens	Medium	120-277 Vac, 50/60 Hz; 125-300 Vdc	IBLLPL8CGMNBU	5


<sup>Ⓛ</sup> Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.




# Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States




## Mercmaster™ Connect LED Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	9500	5000K	Clear Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	MGCL9CP5BU7P	5


## Mercmaster™ LED Generation 3 Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	9500	5000K	Diffused Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	MLGL9CD5BU	10


## Mercmaster LED Low Profile Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	100-277 Vac, 50/60 Hz; 125-300 Vdc	MLLED4CD5BU	15
	7500	5000K	Diffused Polycarbonate Globe	Type V		MLLED7CD5BU	10



## Industrial Mercmaster LED Low Profile Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	100-277 Vac, 50/60 Hz; 125-300 Vdc	IMLLED4CD5BU	10
	7500	5000K	Diffused Polycarbonate Globe	Type V		IMLLED7CD5BU	10




## Contender™ LED Series †

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	VMV5LCD5BU	10

## Mercmaster Accessories

	Description	Catalog Number	Max. Qty.
	Mounting Hood   Pendant   One Hub, Rigid Mounting   3/4" NPT	KPA75	20
	Mounting Hood   Ceiling   Five Hubs, Four Close-Up Plugs   3/4" NPT	KPC75	20
	Mounting Hood   Wall   Five Hubs, Four Close-Up Plugs   3/4" NPT	KPWB75	20
	Mounting Hood   25° Stanchion   One Hub   1-1/2" NPT	KPS150	20
	Mounting Hood   25° Stanchion   One Hub   1-1/4" NPT	KPS125	10
	Mounting Hood   90° Stanchion   One Hub   1-1/2" NPT	KPST150	10
	Mounting Hood Adapter   Crouse-Hinds™ Champ® †   Pendant, Flexible Pendant, Ceiling	MMADCHVS	10
	Mounting Hood Adapter   Crouse-Hinds™ Champ® †   Wall, 25° and 90° Angle Stanchion	MMADCHVA	10
	Visor   Dark Sky Compliant	MMVISOR	10

## Mercmaster and Contender Accessories

	Description	Catalog Number	Max. Qty.
	Globe Guard   Stainless steel wire	MGU1	15
	Safety Cable   Stainless steel	LEDSC	10


① Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.


† Mounts directly to the following Crouse Hinds™ Champ® VMV mounting hoods. | Crouse-Hinds is a registered trademark of Cooper Industries, Inc.




# Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States





Code • Master Accessories			
	Description	Catalog Number	Max. Qty.
	Lens Guard   Stainless Steel Wire	CMLEDGU	5

Rigmaster™ LED Series							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	8000	5000K	Clear Polycarbonate Lens	4 ft   Linear	120-277 Vac, 50/60 Hz; 125-300 Vdc	RMA42CPLBUNGW2	15

Rigmaster Accessories			
	Description	Catalog Number	Max. Qty.
	Safety Cable   Stainless steel	LEDSC	10


Retromaster LED Series							
	Lumens	CCT	Globe Material/Diffusion	Voltage	Catalog Number	Max. Qty.	
	1000 or 2000 (Selectable)	5000K	Diffused Polycarbonate Lens	120-277 Vac, 50/60 Hz	RETROLEDV1BU	5	
	3500 or 5000 (Selectable)	5000K	Diffused Polycarbonate Lens	120-277 Vac, 50/60 Hz	RETROLEDV5BU	5	


Glomaster LED Series							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max Qty
	1000/2000	3000K, 4000K, or 5000K	Diffused Polycarbonate Globe	Type V	120-277Vac, 50/60Hz	GLOLED1QZBU	10
	3500/5000	3000K, 4000K, or 5000K	Diffused Polycarbonate Globe	Type V	120-277Vac, 50/60Hz	GLOLED5QZBU	10

IJL LED Series							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max Qty
	1000/2000	3000K, 4000K, or 5000K	Diffused Polycarbonate Globe	Type V	120-277Vac, 50/60Hz	IJLLED1QZBU	10
	3500/5000	3000K, 4000K, or 5000K	Diffused Polycarbonate Globe	Type V	120-277Vac, 50/60Hz	IJLLED5QZBU	10

HEX LED Series				
	Description	Voltage	Catalog Number	Max. Qty.
	Exit and Emergency Combo   Double-sided, Red Lettering   120 Vac Surge Voltage, 12 Vdc Battery	120-277 Vac, 60 Hz	HEXC122R1212	5

IHC LED Series							
	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	60000	5000K	Clear Polycarbonate Lens	Medium	277-480 Vac, 50/60 Hz	IHCN62CPMBHGP	5

IHC Accessories			
	Description	Catalog Number	Max. Qty.
	Mounting Bracket   Ceiling, Wall, Column, Floor and Conduit Mounting Options   Retrofits with a variety of existing mounting hardware	IHCBRKTL	5

IWL LED Series							
	Lumens	CCT	Lens Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	6000, 8000, or 10000 Selectable	3000K, 4000K, or 5000K Selectable	Diffused Glass Lens	Type III	120-277 Vac, 50/60 Hz	IWL10LZG3BU	5

Ⓢ Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.

