

# Reducing Washers

**NEC/CEC:**  
Listed for Ordinary Locations

## Applications

- To reduce a knockout or siphole in a sheet metal enclosure to a smaller trade size.

## Material

- Steel

## NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E14817
- CSA Standard: C22.2 No. 18.3
- cUL Listed: E14817
- NEMA: FB-1

	Trade Size (Inches)	Dimensions in Millimeters (Inches)			Weight per 100 kg (lb)	Catalog Number
		A	B	C		
<b>Reducing Washers — Steel</b>						
	3/4 to 1/2	34.0 (1.34)	22.4 (0.88)	—	0.54 (1.20)	<b>RW75-50</b>
	1 to 1/2	42.9 (1.69)	22.4 (0.88)	—	1.09 (2.40)	<b>RW100-50</b>
	1 to 3/4	42.9 (1.69)	28.2 (1.11)	—	0.91 (2.00)	<b>RW100-75</b>
	1-1/4 to 1/2	51.6 (2.03)	22.4 (0.88)	—	2.27 (5.00)	<b>RW125-50</b>
	1-1/4 to 3/4	51.6 (2.03)	28.2 (1.11)	—	1.99 (4.40)	<b>RW125-75</b>
	1-1/4 to 1	51.6 (2.03)	35.1 (1.38)	—	1.36 (3.00)	<b>RW125-100</b>
	1-1/2 to 1/2	57.9 (2.28)	22.4 (0.88)	—	2.99 (6.60)	<b>RW150-50</b>
	1-1/2 to 3/4	57.9 (2.28)	28.2 (1.11)	—	2.72 (6.00)	<b>RW150-75</b>
	1-1/2 to 1	57.9 (2.28)	35.1 (1.38)	—	2.27 (5.00)	<b>RW150-100</b>
	1-1/2 to 1-1/4	57.9 (2.28)	43.9 (1.73)	—	1.81 (4.00)	<b>RW150-125</b>
	2 to 1/2	69.9 (2.75)	22.4 (0.88)	—	4.54 (10.00)	<b>RW200-50</b>
	2 to 3/4	69.9 (2.75)	28.2 (1.11)	—	3.63 (8.00)	<b>RW200-75</b>
	2 to 1	69.9 (2.75)	35.1 (1.38)	—	3.63 (8.00)	<b>RW200-100</b>
	2 to 1-1/4	69.9 (2.75)	43.9 (1.73)	—	3.18 (7.00)	<b>RW200-125</b>
	2 to 1-1/2	69.9 (2.75)	50.3 (1.98)	—	2.27 (5.00)	<b>RW200-150</b>

