



# Appleton™ LED Lighting Products | 10 Year Warranty

## Long lifespan — guaranteed.

For safe illumination in harsh industrial and hazardous environments, you need a lighting manufacturer who engineers their luminaires to provide optimal lighting performance under the most extreme conditions. A manufacturer whose luminaires are manufactured with high temperature silicone gaskets, extra surge protection, high quality IP66/IP67 LED drivers, and top tier LEDs, along with patented thermal designs to insure cool operation and long life over a wide operating temperature range.

Emerson is dedicated to developing industry leading LED luminaires that offer superior performance through customized optics, expanded lumen output ranges, and a choice of color temperatures, in designs that are unmatched for their rugged reliability. Our commitment to reliability begins with a rigorous design validation process, where we qualify that our designs perform in environments beyond our worst expectations relative to corrosive atmospheres, extreme temperatures, heavy vibration, and electrical disturbances.

Because Appleton LED luminaires are designed to deliver superior illumination with unparalleled reliability, extending their warranty period reinforces to our customers that Emerson is the right choice for their harsh industrial and hazardous location lighting needs.



Mercmaster™ Connect LED  
Hazardous, Industrial



Mercmaster LED Generation 3  
Hazardous, Zone 1, Industrial



Mercmaster LED Low Profile  
Hazardous, Industrial



Contender™ LED  
Hazardous, Industrial



Code•Master™ LED  
Explosionproof



Code•Master Jr. LED  
Explosionproof



A-51™ LED  
Group C,D



Rigmaster™ LED  
Hazardous, Industrial



Linmaster™ LED  
Zone 1, Zone 2



Explosionproof Rigmaster LED



Baymaster™ LED  
Hazardous, Industrial



IHC LED  
Industrial



Areamaster™ Generation 2 LED  
Hazardous, Zone 1, Industrial

**APPLETON™**

For product information:  
www.masteringled.com  
1.800.621.1506



Emerson offers 10 year warranties on these Appleton LED Luminaires. For full warranty details, exclusions and other relevant information, please refer to the Warranties document located on our website (www.appleton.emerson.com) in the header under “Explore Emerson”. For all other terms and conditions of a sale, please refer to the Terms of Sale document available in the same location.

| Lighting Application | LED Lighting Product Series            | NEC/CEC Certifications |            |        |        |                             |                             |            |            |         |         |         | ATEX/IECEX Certifications     |                               |           |                           | Emergency Battery Backup | Ordinary Location |        |         |         |   |
|----------------------|--|------------------------|------------|--------|--------|-----------------------------|-----------------------------|------------|------------|---------|---------|---------|-------------------------------|-------------------------------|-----------|---------------------------|--------------------------|-------------------|--------|---------|---------|---|
|                      |  | Class I                |            |        |        | Class I, Division 1, Zone 1 | Class I, Division 2, Zone 2 | Class II   |            |         |         |         | Class II, Division 1, Zone 21 | Class II, Division 2, Zone 22 | Class III | ATEX/IECEX Certifications |                          |                   |        |         |         |   |
|                      |  | Division 1             | Division 2 | Zone 1 | Zone 2 |                             |                             | Division 1 | Division 2 | Zone 20 | Zone 21 | Zone 22 |                               |                               |           | Zone 1                    |                          |                   | Zone 2 | Zone 21 | Zone 22 |   |
| Area / Task          | Mercmaster™ Connect LED                |                        | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       |         |         | EFG/IIIC                      | FG                            | ●         |                           | ●                        | ●                 | ●      |         | ●       |   |
|                      | Mercmaster LED Generation 3            |                        | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          |         | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |                           | ●                        | ●                 | ●      |         | ●       |   |
|                      | Mercmaster LED Generation 3 Zone 1     |                        |            | ●      | ●      | IIC                         | IIC                         |            |            |         | ●       | ●       | IIIC                          | IIIB                          |           | ●                         | ●                        | ●                 | ●      |         | ●       |   |
|                      | Mercmaster LED Low Profile             |                        | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG                            | ●         |                           | ●                        | ●                 | ●      |         | ●       |   |
|                      | Contender™ LED                         |                        | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          |         | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |                           |                          |                   |        |         | ●       |   |
|                      | Code•Master™ LED                       | ●                      | ●          | ●      | ●      | BCD/IIIB+H2                 | BCD                         | ●          | ●          |         |         |         | EFG                           | FG                            | ●         |                           |                          |                   |        |         |         | ● |
|                      | Code•Master Jr. LED                    | ●                      | ●          | ●      | ●      | BCD/IIIB+H2                 | BCD                         | ●          |            |         |         |         | EFG                           | FG                            | ●         |                           |                          |                   |        |         |         | ● |
|                      | A-51 LED   Group C, D                  | ●                      | ●          | ●      | ●      | CD                          | CD                          | ●          |            |         |         |         | EFG                           | FG                            | ●         |                           |                          |                   |        |         |         | ● |
|                      | Industrial Mercmaster Connect LED      |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |
|                      | Industrial Mercmaster LED Generation 3 |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |
|                      | Industrial Mercmaster LED Low Profile  |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |
|                      | Industrial Contender LED               |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |
| Linear               | Rigmaster™ LED                         |                        | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |                           |                          |                   |        |         | ●       |   |
|                      | Linmaster LED Zone 2 LED               |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           | ●                        | ●                 | ●      |         | ●       |   |
|                      | Explosionproof Rigmaster LED           | ●                      | ●          | ●      | ●      | CD/IIIB                     | CD/IIIB                     | ●          | ●          |         | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |                           |                          |                   |        |         | ●       |   |
|                      | Linmaster LED Zone 1 LED               |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           | ●                         | ●                        | ●                 | ●      |         | ●       |   |
|                      | Industrial Rigmaster LED               |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |
| High Bay             | Baymaster™ LED                         |                        | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG                            | ●         |                           | ●                        | ●                 | ●      |         | ●       |   |
|                      | Industrial Baymaster LED               |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |
|                      | IHC LED                                |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |
| Floodlight           | Areaster™ Generation 2 LED             |                        | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG                            | ●         |                           | ●                        | ●                 | ●      |         | ●       |   |
|                      | Areaster Generation 2 LED Zone 1       |                        |            | ●      | ●      | IIC                         | IIC                         |            |            |         | ●       | ●       | IIIC                          | IIIC                          |           | ●                         | ●                        | ●                 | ●      |         | ●       |   |
|                      | Industrial Areaster Generation 2 LED   |                        |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |                           |                          |                   |        |         |         | ● |



The Appleton and Emerson logos are registered in the U.S. Patent and Trademark Office. All other product or service names are the property of their registered owners. © February 2025, Appleton Grp LLC. All rights reserved.





## Produits d'éclairage LED Appleton™ | Garantie de 10 ans

### Longue durée de vie — garantie.

Pour une illumination sûre dans des environnements industriels et dangereux, vous avez besoin d'un fabricant d'éclairage qui conçoit ses luminaires pour offrir une performance optimale sous les conditions les plus extrêmes. Un fabricant dont les luminaires sont fabriqués avec des joints en silicone haute température, une protection contre les surtensions renforcée, des drivers LED IP66/IP67 de haute qualité, et des LED de premier choix, ainsi que des conceptions thermiques brevetées pour garantir un fonctionnement frais et une longue durée de vie sur une large plage de températures de fonctionnement.

Emerson s'engage à développer des luminaires LED de premier plan dans l'industrie, offrant une performance supérieure grâce à des optiques personnalisées, des plages de flux lumineux étendues et un choix de températures de couleur, avec des conceptions inégalées pour leur fiabilité robuste. Notre engagement envers la fiabilité commence par un processus rigoureux de validation de conception, où nous vérifions que nos conceptions fonctionnent dans des environnements au-delà de nos pires attentes en ce qui concerne les atmosphères corrosives, les températures extrêmes, les fortes vibrations et les perturbations électriques.

Parce que les luminaires LED Appleton sont conçus pour offrir un éclairage supérieur avec une fiabilité sans pareille, prolonger leur période de garantie renforce auprès de nos clients que Emerson est le choix idéal pour leurs besoins en éclairage industriel sévère et en lieux dangereux.



LED Mercmaster™ connecté  
Zones dangereuses, industrielles



LED Mercmaster 3e génération  
Zones dangereuses, industrielles



LED Mercmaster compacts  
Zones dangereuses, industrielles



LED Contender™  
Zones dangereuses, industrielles



LED Code•Master™  
Antidéflagrant



LED Code•Master Jr.  
Antidéflagrant



LED A-51™  
Groupes C, D



LED Rigmaster™  
Zones dangereuses, industrielles



Linmaster™ Luminaires à LED  
zone 1, zone 2



LED Rigmaster Antidéflagrant



Baymaster™ LED  
Zones dangereuses, industrielles



LED série IHC  
Industriel



LED Areamaster™ 2e génération  
Zones dangereuses, industrielles

**APPLETON™**

Pour plus d'informations sur le produit :  
www.masteringled.com  
1.800.621.1506

**EMERSON™**

Emerson offre 10 ans de garantie sur ces luminaires LED Appleton. Pour les détails complets de la garantie, les exclusions et autres informations pertinentes, veuillez consulter le document sur les garanties disponible sur notre site web ([www.appleton.emerson.com](http://www.appleton.emerson.com)) dans l'en-tête sous « Explore Emerson ». Pour tous les autres termes et conditions de vente, veuillez consulter le document sur les conditions de vente disponible au même endroit.

| Applications d'éclairage | Série de produits d'éclairage LED          | Certifications NEC/CEC |            |        |        |                              |                              |            |            |         |         |                                | Certifications ATEX/IECEx      |            |         |        | Batterie de secours | Zones ordinaires |         |         |         |   |   |
|--------------------------|--|------------------------|------------|--------|--------|------------------------------|------------------------------|------------|------------|---------|---------|--------------------------------|--------------------------------|------------|---------|--------|---------------------|------------------|---------|---------|---------|---|---|
|                          |  | Classe I               |            |        |        | Classe I, Division 1, Zone 1 | Classe I, Division 2, Zone 2 | Classe II  |            |         |         | Classe II, Division 1, Zone 21 | Classe II, Division 2, Zone 22 | Classe III | Zone 1  | Zone 2 |                     |                  | Zone 21 | Zone 22 |         |   |   |
|                          |  | Division 1             | Division 2 | Zone 1 | Zone 2 |                              |                              | Division 1 | Division 2 | Zone 20 | Zone 21 |                                |                                |            |         |        |                     |                  |         |         | Zone 22 |   |   |
| Zone / Classification    | LED Mercmaster™ connecté                   |                        | ●          |        | ●      |                              |                              | ABCD/IIC   | ●          | ●       | ●       |                                |                                | EFG/IIIC   | FG      | ●      |                     | ●                | ●       | ●       | ●       |   | ● |
|                          | LED Mercmaster 3e génération               |                        | ●          |        | ●      |                              |                              | ABCD/IIC   | ●          | ●       |         | ●                              | ●                              | EFG/IIIC   | FG/IIIB | ●      |                     | ●                | ●       | ●       | ●       |   | ● |
|                          | LED Mercmaster 3e génération, Zone 1       |                        |            | ●      | ●      | IIC                          | IIC                          |            |            |         |         | ●                              | ●                              | IIIC       | IIIB    |        | ●                   | ●                | ●       | ●       |         | ● |   |
|                          | LED Mercmaster compact                     |                        | ●          |        | ●      |                              |                              | ABCD/IIC   | ●          | ●       | ●       | ●                              | ●                              | EFG/IIIC   | FG      | ●      |                     | ●                | ●       | ●       | ●       |   | ● |
|                          | LED Contender™                             |                        | ●          |        | ●      |                              |                              | ABCD/IIC   | ●          | ●       |         | ●                              | ●                              | EFG/IIIC   | FG/IIIB | ●      |                     |                  |         |         |         |   | ● |
|                          | LED Code•Master™                           | ●                      | ●          | ●      | ●      | BCD/IIIB+H2                  | BCD                          | ●          | ●          |         |         |                                |                                | EFG        | FG      | ●      |                     |                  |         |         |         |   | ● |
|                          | LED Code•Master Jr.                        | ●                      | ●          | ●      | ●      | BCD/IIIB+H2                  | BCD                          | ●          |            |         |         |                                |                                | EFG        | FG      | ●      |                     |                  |         |         |         |   | ● |
|                          | LED A-51   Groupe C, D                     | ●                      | ●          | ●      | ●      | CD                           | CD                           | ●          |            |         |         |                                |                                | EFG        | FG      | ●      |                     |                  |         |         |         |   | ● |
|                          | Industriels à LED Mercmaster connecté      |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |
|                          | Industriels à LED Mercmaster 3e génération |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |
|                          | Industriels à LED Mercmaster compact       |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |
|                          | Industriels a LED Contender                |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |
| Linéaires                | LED Rigmaster™                             |                        | ●          |        | ●      |                              |                              | ABCD/IIC   | ●          | ●       | ●       | ●                              | ●                              | EFG/IIIC   | FG/IIIB | ●      |                     |                  |         |         |         | ● | ● |
|                          | LED Linmaster LED, zone 2                  |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     | ●                | ●       | ●       | ●       | ● | ● |
|                          | LED Rigmaster antidéflagrant               | ●                      | ●          | ●      | ●      | CD/IIIB                      | CD/IIIB                      | ●          | ●          |         |         | ●                              | ●                              | EFG/IIIC   | FG/IIIB | ●      |                     |                  |         |         |         | ● | ● |
|                          | LED Linmaster, zone 1                      |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        | ●                   | ●                | ●       | ●       | ●       | ● | ● |
|                          | Industriels a LED Rigmaster                |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |
| Montage plafond          | LED Baymaster™                             |                        | ●          |        | ●      |                              |                              | ABCD/IIC   | ●          | ●       | ●       | ●                              | ●                              | EFG/IIIC   | FG      | ●      |                     | ●                | ●       | ●       |         | ● |   |
|                          | Industriels Baymaster                      |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |
|                          | LED série IHC                              |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |
| Projecteurs              | LED Areamaster™ 2e génération              |                        | ●          |        | ●      |                              |                              | ABCD/IIC   | ●          | ●       | ●       | ●                              | ●                              | EFG/IIIC   | FG      | ●      |                     | ●                | ●       | ●       |         | ● |   |
|                          | LED Areamaster 2e génération, zone 1       |                        |            | ●      | ●      | IIC                          | IIC                          |            |            |         |         |                                | ●                              | ●          | IIIC    | IIIC   |                     | ●                | ●       | ●       | ●       |   | ● |
|                          | Areamaster 2e génération industriels à LED |                        |            |        |        |                              |                              |            |            |         |         |                                |                                |            |         |        |                     |                  |         |         |         |   | ● |





## Productos de iluminación LED Appleton™ | Garantía de 10 años

### Larga vida útil - garantizada.

Para una iluminación segura en entornos industriales y peligrosos, necesita un fabricante de iluminación que diseñe sus luminarias para ofrecer un rendimiento óptimo bajo en las condiciones más extremas. Un fabricante cuyas luminarias se fabriquen con juntas de silicona de alta temperatura, protección adicional contra sobretensiones, controladores LED IP66/IP67 de alta calidad y LED de primer nivel, junto con diseños térmicos patentados para garantizar un funcionamiento frío y una larga vida útil en un amplio rango de temperaturas de funcionamiento.

Emerson se dedica a desarrollar luminarias LED líderes en el sector que ofrecen un rendimiento superior a través de ópticas personalizadas, rangos de salida de lúmenes ampliados y una selección de temperaturas de color, en diseños que no tienen parangón por su fiabilidad robusta. Nuestro compromiso de ofrecer fiabilidad comienza con un riguroso proceso de validación del diseño, donde determinamos que nuestros diseños funcionan en entornos que superan nuestras peores expectativas en relación con atmósferas corrosivas, temperaturas extremas, fuertes vibraciones y perturbaciones eléctricas.

Dado que las luminarias LED Appleton están diseñadas para ofrecer una iluminación superior con una fiabilidad inigualable, la extensión de su periodo de garantía, refuerza ante nuestros clientes que Emerson es la mejor opción para sus duras necesidades de iluminación industrial y en ubicaciones peligrosas.



LED Mercmaster™ Connect  
Peligrosos, Industriales



LED Mercmaster Generación 3  
Peligrosos, Zona 1, Industriales



LED Mercmaster perfil sencillo  
Peligrosos, Industriales



LED Contender™  
Peligrosos, Industriales



Code•Master™ LED  
Prueba de explosión



Code•Master Jr. LED  
Prueba de explosión



A-51™ LED  
Grupos A, B, C, D, Grupo C, D



Rigmaster™ LED  
Peligrosos, Industriales



Linmaster™ LED  
Zona 1, Zona 2



Rigmaster LED  
Prueba de Explosión



Baymaster™ LED  
Peligrosos, Industriales



IHC LED  
Industriales



Areamaster™ Generation 2 LED  
Peligrosos, Zona 1, Industriales

**APPLETON™**

Para obtener información sobre el producto:  
www.masteringled.com  
1.800.621.1506

**EMERSON™**

Emerson ofrece 10 años de garantía para estas luminarias LED Appleton. Para obtener todos los detalles de la garantía, exclusiones y otra información relevante, consulte el documento de Garantías disponible en nuestro sitio web ([www.appleton.emerson.com](http://www.appleton.emerson.com)) en el encabezado "Explore Emerson". Para todos los demás términos y condiciones de venta, consulte el documento Términos de venta disponible en la misma ubicación.

| Aplicación de iluminación                   | Serie de productos de iluminación LED    | Certificaciones NEC/CEC |            |        |        |                             |                             |            |            |         |         |         |                               | Certificaciones ATEX/IECEX    |           |        |        | Batería de Emergencia | Ubicaciones comunes |         |         |   |
|---|--|-------------------------|------------|--------|--------|-----------------------------|-----------------------------|------------|------------|---------|---------|---------|-------------------------------|-------------------------------|-----------|--------|--------|-----------------------|---------------------|---------|---------|---|
|   |  | Clase I                 |            |        |        | Clase I, División 1, Zona 1 | Clase I, División 2, Zona 2 | Clase II   |            |         |         |         | Clase II, División 1, Zona 21 | Clase II, División 2, Zona 22 | Clase III | Zona 1 | Zona 2 |                       |                     | Zona 21 | Zona 22 |   |
|   |  | División 1              | División 2 | Zona 1 | Zona 2 |                             |                             | División 1 | División 2 | Zona 20 | Zona 21 | Zona 22 |                               |                               |           |        |        |                       |                     |         |         |   |
| Área / Tarea                                | LED Mercmaster™ Connect                  |                         | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       |         |         | EFG/IIIC                      | FG                            | ●         |        | ●      | ●                     | ●                   |         | ●       |   |
|   | LED Mercmaster Generation 3              |                         | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          |         | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |        | ●      | ●                     | ●                   |         | ●       |   |
|   | LED Mercmaster Generation 3 zona 1 serie |                         |            | ●      | ●      | IIC                         | IIC                         |            |            |         | ●       | ●       | IIIC                          | IIIB                          |           | ●      | ●      | ●                     | ●                   |         | ●       |   |
|   | LED Mercmaster perfil sencillo           |                         | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG                            | ●         |        | ●      | ●                     | ●                   |         | ●       |   |
|   | LED Contender™                           |                         | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          |         | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |        |        |                       |                     |         | ●       |   |
|   | LED Code•Master™                         | ●                       | ●          | ●      | ●      | BCD/IIIB+H2                 | BCD                         | ●          | ●          |         |         |         | EFG                           | FG                            | ●         |        |        |                       |                     |         |         | ● |
|   | LED Code•Master Jr.                      | ●                       | ●          | ●      | ●      | BCD/IIIB+H2                 | BCD                         | ●          |            |         |         |         | EFG                           | FG                            | ●         |        |        |                       |                     |         |         | ● |
|   | A-51 LED   Grupo C, D                    | ●                       | ●          | ●      | ●      | CD                          | CD                          | ●          |            |         |         |         | EFG                           | FG                            | ●         |        |        |                       |                     |         |         | ● |
|   | Industriales LED Mercmaster Connect      |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         |         | ● |
|   | Industriales LED Mercmaster Generation 3 |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         |         | ● |
| Industriales LED Mercmaster perfil sencillo |  |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         | ●       |   |
| Industriales LED Contender                  |  |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         | ●       |   |
| Lineal                                      | LED Rigmaster™                           |                         | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |        |        |                       |                     |         | ●       |   |
|   | LED Linmaster Serie Zona 2               |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        | ●      | ●                     | ●                   |         | ●       |   |
|   | Rigmaster LED Prueba de Explosión        | ●                       | ●          | ●      | ●      | CD/IIIB                     | CD/IIIB                     | ●          | ●          |         | ●       | ●       | EFG/IIIC                      | FG/IIIB                       | ●         |        |        |                       |                     |         | ●       |   |
|   | LED Linmaster Serie Zona 1               |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           | ●      | ●      | ●                     | ●                   |         | ●       |   |
|   | Industriales LED Rigmaster               |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         |         | ● |
| Grandes Alturas                             | LED Baymaster™                           |                         | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG                            | ●         |        | ●      | ●                     | ●                   |         | ●       |   |
|   | Industriales LED Baymaster               |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         |         | ● |
|   | LED IHC                                  |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         |         | ● |
| Reflector                                   | Areamaster™ Generation 2 LED             |                         | ●          |        | ●      |                             | ABCD/IIC                    | ●          | ●          | ●       | ●       | ●       | EFG/IIIC                      | FG                            | ●         |        | ●      | ●                     | ●                   |         | ●       |   |
|   | Areamaster Generation 2 y Zona 1 LED     |                         |            | ●      | ●      | IIC                         | IIC                         |            |            |         | ●       | ●       | IIIC                          | IIIC                          |           | ●      | ●      | ●                     | ●                   |         | ●       |   |
|   | Industriales LED Areamaster Generation 2 |                         |            |        |        |                             |                             |            |            |         |         |         |                               |                               |           |        |        |                       |                     |         |         | ● |