
EVERSON

Adaptable Engineering for User Versatility


with Appleton[™] Glomaster[™] and IJL LED series

GLOMASTER AND IJL LED SERIES MULTIFACETED LED SOLUTION





CERTIFIED FOR YOUR NEEDS Available for hazardous locations and heavy industrial locations



FIELD SELECTABL **TECHNOLOGY**

Each model offers the added benefit of field selectable lumen levels and Correlated Color Temperature (CCT)

SIMPLIFIED INSTALLATION

Multi-mounting ability within one fixture – wall, ceiling or pendant

GLOMASTER AND IJL LED SERIES ALL-IN-ONE FIXTURES

ADJUSTABLE ARM

User can direct the light in 10° increments regardless of orientation

FIELD SELECTABLE TECHNOLOGY

Easily adjust the lumen levels and Correlated Color Temperature (CCT) to meet the users needs

EFFICIENT LIGHTINING

Specially design optics for optimal light distribution including uplight

Relevant Industries



Manufacturing




Construction





Foundry




Metal & Mining










AppletonTM Glomaster & IJL LED Series



The Appleton[™] Glomaster and IJL LED series are highly versatile for hazardous and heavy industrial locations. With user selectable technology, it allows one to choose from a range of color temperatures and/or lumen outputs. Along with a multi-faceted mounting hood, they are the most optimal lighting solutions for a variety of applications.



APPLETON

Learn more at www.masteringled.com

©2024 Emerson Electric Co. All rights reserved.